ULTRAFILTRATION SYSTEMS



BraneWave UF Field Test Kit (P/N UF-INLINE-FT-KIT)

BRANEWAVE UF FIELD TEST KIT INCLUDES:

- (1) BraneWave UF Field Test Module
- (2) Female Adapters, 1 inch FBSP x 1 inch ASTM spigot, Sch40 PVC
- (2) Reducer Bushings, 1 inch spigot x 3/4 inch FPT, Sch80 PVC
- (2) Reducer Bushings, 3/4 inch MPT x 1/4 inch FPT, Sch80 PVC
- (2) Plugs, 3/4 inch MPT, Sch80 PVC
- (1) Coupling, 3/4 inch MPT or 1/2 inch FPT x 3/4 inch garden hose, brass
- (1) Diverter Valve Kit with 1/4 inch elbow
- (1) Diverter Adapter, 15/16 inch, brass
- (1) Diverter Adapter, 13/16 inch, brass
- (1) Long Reach Spout with 1/4 inch elbow, chrome plated

BRANEWAVE™ UF FIELD TEST KIT 0.02 MICRON ULTRAFILTRATION

SWT's **BraneWave UF Field Test Kit** is designed to quickly and dramatically demonstrate the results of installing a BraneWave UF System on a subject water application with visible particles (including sediment or tannin). For tannin removal, since the molecular weights vary widely, it is especially important that the filtration level be determined prior to a full-system installation. Using the necessary combination of fittings included with the test kit, attach the BraneWave UF Field Test Module to an untreated faucet and run the water through the module. Clear, clean water indicates immediately that the tannin problem can be successfully solved with a BraneWave UF System. It's that quick and simple.

FEATURES AND BENEFITS

- Demonstrates effectiveness of BraneWave Ultrafiltration System
- Installs quickly and easily to faucet
- All hardware included, no tools necessary
- Determines tannin removal ability of BraneWave UF System prior to installation
- Requires only water pressure to operate, no pump necessary

The **BraneWave UF Field Test Module** is a hollow fiber ultrafilter installed within a 1.25×8 inch polypropylene sleeve with specified inlet and outlet ends.

BRANEWAVE UF FIELD TEST MODULE SPECIFICATIONS:

Filtration Level: 0.02 micron
Operating Temperature:
Operating Pressure (Inlet): 10 to 100 psi (0.68 to 6.8 bar)
Continuous Flow Rate: 0.84 gpm at 50 psi and 68°F (20°C) 0.68 gpm at 40 psi and 68°F (20°C)
End Openings: 1 inch male BSP

Shipped with protective end caps and a preservative solution of Glycerine and Metabisulfite.

